



Parallel Jaw Grip 2-1/2-Inch Length



Lightweight, compact grips pull an exceptionally wide range of cable sizes and types. Designed with a round inside-jaw contour for maximum contact to minimize conductor damage. Lower jaw is serrated to firmly grip insulated cables and conductors. Design includes a latch that prevents the grip from falling in case of jaw disengagement from the cable.

Specifications

Type:	Parallel Jaw Grip	Application:	Wire Pulling
Special Features:	Spring	Overall Length:	9.52" (24.2 cm)
Overall Height:	5.31" (13.5 cm)	Overall Width:	1.22" (3.1 cm)
Material:	Steel	Cable Type:	Messenger, EHS, Coated
Cable Diameter:	0.157" to 0.875" (3.98 to 22.22 mm)	Hot Latch:	N
Swing Latch:	N	Spring:	Y
Locking Handle:	N	Jaw Type:	Round
Teeth Type:	Coarse	Jaw Length:	2.5" (6.4 cm)
Maximum Safe Load:	4500 lb (2041 kg)	Weight:	2.6 lb (1.2 kg)