



Parallel Jaw Grip 4-1/2-Inch Length



Lightweight, compact grips pull an exceptionally wide range of cable sizes and types. Designed with a round inside-jaw contour for maximum contact to minimize conductor damage. Lower jaw is serrated to firmly grip insulated cables and conductors. Design includes a latch that prevents the grip from falling in case of jaw disengagement from the cable.

Specifications

| | | | |
|--------------------|-------------------------------------|-----------------|----------------------------|
| Type: | Parallel Jaw Grip | Application: | Wire Pulling |
| Special Features: | Hot Latch, Spring | Overall Length: | 11.7" (29.7 cm) |
| Overall Height: | 6.4" (16.3 cm) | Overall Width: | 2.4" (6.1 cm) |
| Material: | Steel | Cable Type: | Messenger, EHS, Guy Strand |
| Cable Diameter: | 0.625" to 1.25" (15.87 to 31.75 mm) | Hot Latch: | Y |
| Swing Latch: | N | Spring: | Y |
| Locking Handle: | N | Jaw Type: | Round |
| Teeth Type: | Coarse | Jaw Length: | 4.5" (11.4 cm) |
| Maximum Safe Load: | 7500 lb (3400 kg) | Weight: | 4.8 lb (2.2 kg) |