



Knurled Parallel Jaw Grip 4-3/8-Inch Length



Longer knurled jaws achieve a firm hold, reducing possibility of slippage and damage to cable. Design includes a latch, plus a large-diameter eye that accommodates large hooks on hoists, winches and tackle blocks. When latch is closed, it helps maintain cable position in grip jaws.

Specifications

Type:	Parallel Jaw Grip	Application:	Wire Pulling
Special Features:	Longer Jaw and Large Diameter Eye	Overall Length:	7.2" (18.3 cm)
Material:	Steel	Cable Type:	Aircraft, Messenger, Guy Strand
Cable Diameter:	0.2" to 0.4" (5.08 to 10.16 mm)	Hot Latch:	N
Swing Latch:	N	Spring:	N
Locking Handle:	N	Jaw Type:	Double V
Teeth Type:	Coarse	Jaw Length:	4.375" (11.1 cm)
Maximum Safe Load:	10,000 lb (4536 kg)	Weight:	4.6 lb (2.1 kg)