



Chicago® Grip Bell-System Type Grip



Designed for use on aluminum, copper, weatherproof coated wire, PVC covered conductors and messenger and guy strand. The Chicago style grip was designed for cable sizes from 0.12-Inch to 1.0-Inch (3.10 to 25.4 mm). Equipped with chain, toggle and shackle. For support wire 0.134-Inch and larger, refer to 1659 series. Outside diameter of support wire includes thickness of polyethylene coating.

Specifications

| | | | |
|--------------------|------------------------------------|--------------|-----------------------|
| Type: | Chicago Grip | Application: | Wire Pulling |
| Material: | Steel | Cable Type: | Messenger, Guy Strand |
| Cable Diameter: | 0.218" to 0.55" (5.54 to 13.97 mm) | Hot Latch: | N |
| Swing Latch: | N | Spring: | Y |
| Locking Handle: | Y | Jaw Type: | Double V |
| Teeth Type: | Smooth | Jaw Length: | 5" (12.7 cm) |
| Maximum Safe Load: | 8000 lb (3629 kg) | Weight: | 6.6 lb (2.99 kg) |