



# 1000V Insulated Utility Tool Kit in Hard Case, 13-Piece



The Utility Insulated tool kit features 13 of the essential tools the Lineman needs. The custom case includes 2 pallets with pockets custom-fit for each tool, a piano-hinged case cover that has both a combination lock and two key-locked latches for security. This hardcase also has extra storage space behind the pallets for important papers or other accessories.

## Specifications

|                  |                                                                                                                                                                  |                   |                                |
|------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------|--------------------------------|
| Application:     | General Application Near Energized Source                                                                                                                        | Special Features: | Includes Combination Lock Case |
| Included:        | D2000-9NE-INS; D2000-28-INS; D2000-48-INS; D203-8-INS; 602-4-INS; 602-7-INS; 602-8-INS; 633-4-INS; 603-4-INS; 633-7-INS; 63050-INS; D502-10-INS; 1571-INS; 33535 | Insulated:        | Yes                            |
| Handle Material: | High-Dielectric Plastic                                                                                                                                          | Handle Color:     | Orange                         |
| Overall Length:  | 15.375" (39.1 cm)                                                                                                                                                | Overall Height:   | 8.25" (21 cm)                  |
| Overall Width:   | 18.875" (47.9 cm)                                                                                                                                                | Standard:         | IEC 60900: 2012, ASTM F1505-10 |
| Weight:          | 20.1 lb (9.1 kg)                                                                                                                                                 |                   |                                |