



MODbox™ Rechargeable Worklight



The MODbox™ Area Light is a work light designed for any jobsite, with up to 1000 Lumens of output. The portable light has a MODbox™ compatible kickstand which includes 4 powerful magnets and a nail notch to mount light for hands-free use. These versatile mounting features along with a 360-Degree rotating light head allow users to direct the light where needed. The area light has 3 light output modes, with a run time of up to 21 hours and is impact-resistant, capable of surviving a 9-Foot drop.

Specifications

Type:	Work Light	Application:	Medium Spread Light Coverage
Special Features:	Pivoting Hinge, Rotating Head, Magnets, Nail Hole	Material:	Plastic
Color:	Orange/Black	Bulb Type:	LED
Lumens:	Per Mode; 1000, 425, or 300	Battery Life:	Per Mode: 9, 14, or 21 hr
Batteries:	Lithium-Ion	Temperature Range:	-4? to 122? F (-20? to 50? C)
Drop Protection:	9.8' (3 m)	Water Resistant:	Yes
Strobing:	No	Shock Resistant:	No
Miniature:	No	Included:	Charging Cable
Overall Height (Inch):	4.59	Overall Height (cm):	11.7
Overall Length (Inch):	3.59	Overall Length (cm):	9.1
Overall Width (Inch):	2.71	Overall Width (cm):	6.9
Weight (g):	549	Weight (oz):	19.36