



Insulated Screwdriver, #3 Phillips, 7-Inch Round Shank



Protect yourself when working near an energized source. Clearly marked with the official 1000-Volt rating symbol, Klein insulated tools exceed IEC 60900 and ASTM F1505 standards for insulated tools. 2 layers of insulation provide protection against electric shock. Built to handle the tough jobs with ease.

Specifications

Application:	For Work Near Energized Sources	Special Features:	Flame Retardant and Impact Resistant Handle
Tip Type:	Phillips	Magnetic:	No
Tip Size:	#3	Shank Type:	Round
Shank Length:	7" (17.8 cm)	Material:	Induction Hardened Steel
Insulated:	Yes	Handle Material:	High-Dielectric Plastic
Handle Color:	Black	Overall Length:	12.375" (31.4 cm)
Standard:	IEC 60900 and ASTM F1505	Weight:	6.4 oz (181 g)