



High-Tension Hacksaw



Klein Tools 12-Inch (30 cm) High-Tension Hacksaw has adjustable blade tension up to 30,000 Pounds Per Square Inch for fast, precise cuts. Includes 12-Inch (305 mm) x 24 Teeth Per Inch bi-metal hack saw blade and 6-Inch (152 mm) x 24 Teeth Per Inch bi-metal reciprocating saw blade. Also has convenient blade storage in handle and soft touch grips.

Specifications

Type:	High Tension	Application:	Alternative 45 Degree Mounting for Flush Cutting
Teeth Per Inch:	24	Blade Length (Inch):	12
Blade Length (cm):	30.5	Overall Length (Inch):	16.25
Overall Length (cm):	41.3	Blade Material:	Bi-Metal
Weight (oz):	24	Weight (g):	680