



Pliers, Needle Nose Side-Cutters with Spring, 6-Inch



These Long-Nose Side-Cutters are spring-loaded for self-opening. The cutting knives are induction hardened for maximum life. Made of forged steel for durability with a long nose for grabbing and looping wire.

Specifications

Type:	Long Nose Side Cutting Pliers	Overall Length:	6.68" (17 cm)
Jaw Length:	1.969" (5 cm)	Jaw Width:	0.688" (1.7 cm)
Jaw Thickness:	0.375" (1 cm)	Jaw Capacity:	1.72" (4.4 cm)
Point Diameter:	0.094" (0.24 cm)	Knife Length:	0.572" (1.5 cm)
Handle Color:	Yellow	Handle Finish:	Plastic-Dipped
Handle Length:	3.43" (8.7 cm)	Insulated:	No
Weight:	4.3 oz (122 g)		