



## Side Cutting Pliers, New England Insulated, 9-Inch



These Klein Tools Side Cutting New England Insulated Pliers are insulated by two layers and pass both the IEC 60900 and ASTM F1505 standards. They are made of forged steel with induction-hardened knives for strength and durability. And they have high-leverage design which provides 46-percent more cutting and gripping power than other plier designs.

### Specifications

Type:	Side Cutting Pliers	Application:	ACSR, Screws, Nails and Most Hardened Wires
Special Features:	Integral Guards Help Prevent Hand Contact With Conductive Parts	Overall Length:	9.68" (24.6 cm)
Overall Width:	2.49" (6.3 cm)	Material:	Induction Hardened Steel
Nose Type:	New England	Jaw Length:	1.91" (4.9 cm)
Jaw Width:	1.25" (3.2 cm)	Jaw Thickness:	0.62" (1.6 cm)
Jaw Capacity:	1.375" (3.5 cm)	Cutting Knives:	1
Knife Length:	0.781" (2 cm)	Cut Style:	Side-Cutting
Screw Shearing:	No	Joint Type:	Hot-Riveted
Handle Color:	Orange	Handle Finish:	2-Layer Insulation
Handle Length:	5.73" (14.6 cm)	Insulated:	Yes
Tether Capable:	No	Standards:	IEC 60900 and ASTM F1505
Weight:	1.25 lb (0.6 kg)		