



Diagonal Cutting Pliers, Insulated, 7-Inch



These Insulated Diagonal-Cutting pliers have dual layered grips that are flame retardant, impact resistant, and rated for 1000-volts. They feature a tapered nose design with induction hardened cutting knives for durability. They are made of forged steel and have a hot-riveted joint for smooth action and no handle wobble.

Specifications

Type:	Diagonal Cutting Pliers	Special Features:	Flame Retardant and Impact Resistant Handle
Overall Length (Inch):	7.67	Overall Length (cm):	19.5
Material:	Induction Hardened Steel	Nose Type:	Tapered
Jaw Length (Inch):	1	Jaw Length (cm):	2.5
Jaw Width (Inch):	0.969	Jaw Width (cm):	2.5
Jaw Thickness (Inch):	0.5	Jaw Thickness (cm):	1.3
Jaw Capacity (Inch):	1.1	Jaw Capacity (cm):	2.8
Cutting Knives:	Standard	Cut Style:	Diagonal-Cutting
Joint Type:	Hot-Riveted	Handle Color:	Orange
Handle Finish:	2-Layer Insulation	Handle Length (Inch):	4.34
Handle Length (cm):	11	Insulated:	Yes
Standard:	IEC 60900 and ASTM F1505	Weight (oz):	11.2
Weight (g):	318		