



Diagonal Cutting Pliers, High-Leverage, 7-Inch



These Diagonal-Cutting Pliers have a high-leverage design to provide 36-Percent greater cutting power than other pliers. The hot-riveted joint ensures smooth action with no handle wobble. Klein Tools specializes in making some of the world's finest pliers.

Specifications

Type:	Diagonal Cutting Pliers	Application:	General Purpose
Special Features:	Laser Hardened Knives	Overall Length (Inch):	7
Overall Length (cm):	17.8	Overall Height (Inch):	0.438
Overall Height (cm):	1.1	Material:	Steel
Nose Type:	Angled	Jaw Length (Inch):	0.779
Jaw Length (cm):	2	Jaw Width (Inch):	1.25
Jaw Width (cm):	3.2	Jaw Thickness (Inch):	0.46
Jaw Thickness (cm):	1.2	Jaw Capacity (Inch):	1.031
Jaw Capacity (cm):	2.6	Cutting Knives:	Standard
Knife Length (Inch):	0.781	Knife Length (cm):	2
Cut Style:	Standard	Joint Type:	Hot Riveted
Handle Color:	Orange	Handle Finish:	Plastic-Dipped
Handle Length (Inch):	3.75	Handle Length (cm):	9.5
Insulated:	No	Tether Capable:	No
Standard:	Yes	Weight (oz):	8.6

Weight (g):	244
-------------	-----