



Diagonal Cutting Pliers, Insulated, High Leverage, 8-Inch



These High-Leverage Insulated Diagonal-Cutting pliers are 1000V rated for safety on the job. The thick, exceptionally tough white inner layer coating is bonded to the tool. Integral thumb guards prevent hand contact with conductive parts. The bright orange handles make this tool comfortable to use all day and easy to identify in the field. The durable, molded insulation meets or exceeds IEC 60900 and ASTM F1505 standards for insulated tools. Cutting knives are induction hardened for long life.

Specifications

Type:	Diagonal Cutting Pliers	Application:	ACSR, Screws, Nails and Most Hardened Wire
Special Features:	Flame Retardant and Impact Resistant Handle	Overall Length:	8.24" (20.9 cm)
Material:	Induction Hardened Steel	Nose Type:	Tapered
Jaw Length:	0.781" (2 cm)	Jaw Width:	1.25" (3.2 cm)
Jaw Thickness:	0.46" (1.2 cm)	Cutting Knives:	Standard
Cut Style:	Diagonal-Cutting	Joint Type:	Hot-Riveted
Handle Color:	Orange	Handle Finish:	2-Layer Insulation
Handle Length:	4.9" (12.4 cm)	Insulated:	Yes
Standard:	IEC 60900 and ASTM F1505	Weight:	11.2 oz (318 g)