



# Electronics Pliers, Needle Nose with Curved Chain-Nose, 5-Inch



The 60-degree bent nose on these Midget Curved Chain-Nose pliers provide maximum work visibility in confined areas. This tool easily bends and forms fine wire. Polished inside jaws and radiused jaw edges prevent nicking wire while the curved handles provide greater tool control. Made of forged steel for maximum durability.

## Specifications

|                      |                  |                        |            |
|----------------------|------------------|------------------------|------------|
| Type:                | Long Nose Pliers | Overall Length (Inch): | 4.75       |
| Overall Length (cm): | 12.1             | Jaw Length (Inch):     | 1          |
| Jaw Length (cm):     | 2.5              | Jaw Width (Inch):      | 0.406      |
| Jaw Width (cm):      | 1                | Jaw Thickness (Inch):  | 0.25       |
| Jaw Thickness (cm):  | 0.6              | Jaw Type:              | Flat       |
| Jaw Texture:         | Smooth           | Jaw Capacity (Inch):   | 1.28       |
| Jaw Capacity (cm):   | 3.3              | Point Diameter (Inch): | 0.05       |
| Point Diameter (cm): | 0.1              | Handle Color:          | Light Blue |
| Handle Finish:       | Plastic-Dipped   | Handle Length (Inch):  | 2.65       |
| Handle Length (cm):  | 6.7              | Insulated:             | No         |
| Weight (oz):         | 2.1              | Weight (g):            | 60         |