



## Journeyman™ Side-Cutters, 8-Inch



These high-leverage side cutters provide 46-Percent more cutting and gripping power than other pliers. Dual-material Journeyman handles provide a better grip without sacrificing tool strength and durability. Hot-riveted joint ensures smooth action and no handle wobble. Induction hardened cutting knives for long life.

### Specifications

Type:	Side Cutting Pliers	Overall Length:	8.89" (22.6 cm)
Material:	Steel	Nose Type:	New England
Jaw Length:	1.441" (3.7 cm)	Jaw Width:	1.209" (3.1 cm)
Jaw Thickness:	0.613" (1.6 cm)	Jaw Capacity:	1.625" (4.1 cm)
Knife Length:	0.719" (1.8 cm)	Cut Style:	Flush
Joint Type:	Adjustable	Handle Color:	Dark Blue/Black
Handle Finish:	Journeyman™ Dual-Material	Handle Length:	5.07" (12.9 cm)
Insulated:	No	Tether Capable:	No
Weight:	15.5 oz (440 g)		