



Diagonal Cutting Pliers, Journeyman, 8-Inch



These Diagonal Cutters have a high-leverage design for 36-Percent more cutting power than other pliers. State-of-the-art, dual-material Journeyman™ handles provide a better grip without sacrificing tool strength and durability. Short jaws and beveled cutting edges let you cut wire closely. The hot-riveted joint ensures smooth action and no handle wobble while the cutting knives are induction-hardened for long life.

Specifications

Type:	Diagonal Cutting Pliers	Overall Length (Inch):	8
Overall Length (cm):	20.3	Material:	Steel
Jaw Length (Inch):	0.781	Jaw Length (cm):	2
Jaw Width (Inch):	1.25	Jaw Width (cm):	3.2
Jaw Thickness (Inch):	0.46	Jaw Thickness (cm):	1.2
Jaw Capacity (Inch):	1	Jaw Capacity (cm):	2.5
Cutting Knives:	Standard	Cut Style:	Standard
Joint Type:	Adjustable	Handle Color:	Red/Black
Handle Finish:	Journeyman™ Dual-Material	Handle Length (Inch):	4.7
Handle Length (cm):	11.9	Insulated:	No
Tether Capable:	No	Standard:	Yes
Weight (oz):	10.7	Weight (g):	303