



Extra-Capacity Adjustable Wrench, 10-Inch



Klein Tools' 10-Inch (250 mm) Extra Capacity Adjustable Wrench is made of forged, heat-treated alloy steel for maximum strength and light weight. Jaws are precision-machined to ensure smooth operation. Contoured, plastic-dipped handles make them easy to grip and comfortable to use.

Specifications

Type:	Adjustable Wrench	Application:	Torquing Nuts and Bolts
Special Features:	Extra Capacity Jaw; Forged Steel; Laser Engraved Inch and mm Scales; Soft Dipped Grips; Hang Holes	Jaw Capacity (Inch):	1.48
Jaw Capacity (cm):	3.8	Reversible:	Yes
Overall Length (Inch):	10.25	Overall Length (cm):	26
Overall Height (Inch):	0.6	Overall Height (cm):	1.5
Overall Width (Inch):	2.69	Overall Width (cm):	6.8
Material:	6140 Forged Steel	Handle Color:	Orange Pantone 165C
Handle Finish:	Plastisol Dipped	Handle Length:	7.5" (19 cm)
Standard:	ASME B107.100	Weight (lb):	1.03
Weight (kg):	0.5		