



Extra-Capacity Adjustable Wrench, 12-Inch



Klein Tools' 12-Inch Extra-Capacity Adjustable Wrench is made of forged, heat-treated alloy steel for maximum strength and light weight. Jaws are precision-machined to ensure smooth operation. Contoured, plastic-dipped handles make them easy to grip and comfortable to use.

Specifications

Type:	Adjustable Wrench	Application:	Torquing Nuts and Bolts
Special Features:	Extra-Capacity Jaw; Forged Steel; Laser Engraved SAE and Metric Scales; Soft Dipped Grips; Hang Holes	Jaw Capacity:	1.74" (4.4 cm)
Reversible:	Yes	Overall Length:	12.25" (31.1 cm)
Overall Height:	0.70" (1.8 cm)	Overall Width:	3.13" (8 cm)
Material:	6140 Forged Steel	Handle Color:	Orange Pantone 165C
Handle Finish:	Plastisol Dipped	Handle Length:	9" (22.7 cm)
Standard:	ASME B107.100	Weight:	1.83 lb (0.83 kg)