



## Chicago Grip, Forged, Hot-Line, .218 to .55-Inch



The Klein S1684-5H Chicago Grip-with Hot-Line Latch for Bare Conductors are for both bare and insulated conductors. The Klein S1684-5H Chicago Grip-with Hot-Line Latch for Bare Conductors grip may be placed on wire with hot-line stick. When stick is removed, latch closes automatically to guard against grip accidentally disengaging from wire.

### Specifications

Type:	Chicago Grip	Application:	Wire Pulling
Overall Length:	14.75" (37.5 cm)	Overall Height:	8.63" (21.9 cm)
Overall Width:	2.38" (6 cm)	Material:	Steel
Cable Type:	Aircraft, EHS, Messenger, Guy Strand	Cable Diameter:	0.218" to 0.55" (5.54 to 13.97 mm)
Hot Latch:	Y	Swing Latch:	N
Spring:	Y	Locking Handle:	Y
Jaw Type:	Double V	Teeth Type:	Smooth
Jaw Length:	5" (12.7 cm)	Maximum Safe Load:	8000 lb (3629 kg)
Weight:	6.7 lb (3.0 kg)		