



Pliers, Connector Crimping Needle Nose, 7-Inch



These Connector Crimping Long-Nose Pliers are designed to crimp Scotchlok® type connectors. These pliers also have grooved jaws which are great for wire wrapping, looping, and twisting. It can also cleanly strip 23 AWG and 24 AWG wire.

Specifications

Type:	Long Nose Pliers	Application:	Crimps UR/UY/UG Insulation Displacement Connectors (IDC)- Scotchlok Type Connectors, Cleanly Strips 23 AWG and 24 AWG Wires
Overall Length (Inch):	6.68	Overall Length (cm):	17
Jaw Length (Inch):	2	Jaw Length (cm):	5.1
Jaw Width (Inch):	0.5	Jaw Width (cm):	1.3
Jaw Thickness (Inch):	0.36	Jaw Thickness (cm):	0.9
Point Diameter (Inch):	0.125	Point Diameter (cm):	0.3
Knife Length (Inch):	0.44	Knife Length (cm):	1.1
Handle Color:	Yellow	Handle Finish:	Plastic-Dipped
Handle Length (Inch):	3.43	Handle Length (cm):	8.7
Insulated:	No	Standard:	Yes
Weight (oz):	4.5	Weight (g):	128
Crimps:	Yes		