


発注品番	タイプ	θ	駆動ボルト 規格寸法	A	B	C	D	E	F	G	H	K	M	R ₁	R ₂	O	T	材質	組立	備考	
7003-6000	ストリート	—	30	8	9	19	39.5	39	14.5	15.1	18	37	—	24	4.5	5.4	14	2.3	DK-3-3H	SNX9#	無
7003-6001	ストリート	—	40	8	9	19	39.5	42	14.5	16.6	20	41.1	—	24	5	5.7	14	2.3	D8000H	SNX9#	無
7003-6002	ストリート	—	40	10	11	19	39.5	42	14.5	16.6	20	41.1	—	24	5	5.7	14	2.3	D8000H	SNX9#	無
7003-6005-02	ストリート	—	40	10	11	19	39.5	42	14.5	16.6	20	41.1	—	24	5	5.7	14	2.3	C8001P	SNX9#	無
7003-6008-02	ストリート	—	60	8	9	20	49.5	47	15	19.5	24	48.4	—	24.5	6	6.8	15	2.5	D8000H	SNX9#	無
7003-6003	ストリート	—	60	10	11	20	49.5	47	15	19.5	24	48.4	—	24.5	6	6.8	15	2.5	D8000H	SNX9#	無
7003-6300	上通好	60	60	8	9	20	49.5	47	15	19.5	24	48.4	18	24.5	6	6.8	15	2.5	D8000H	SNX9#	有
7003-6400	上通好	90	30	10	11	19	54.2	39	14.5	15.1	18	37	24.2	24	4.5	5.4	14	2.3	DK-3-3H	SNX9#	有
7003-6401	上通好	90	30	12	13	20	71.5	39	14.5	15.1	18	37	39.7	24	4.5	5.4	14	2.3	D8000H	SNX9#	有
7003-6812-02	下通好	70	15	8	9	19	66.2	27	13	11	14	26.3	35	3	3.5	13	2	C8001P	SNX9#	無	
7003-6813-02	下通好	70	30	8	9	19	65.7	39	14.5	15.1	18	37	35	24	4.5	5.4	14	2.3	C8001P	SNX9#	無
7003-6800-02	下通好	90	20	8	9	19	57.7	30	13	12	16	33	15	23	3.5	4.1	13	2	C8100H	SNX9#	無

7003-206862-Nは、
標準品ではない。 別図を参照。


E

D



断面 X-X(2/1)

C



断面 Y-Y(2/1)

B

A

CUSTOMER	CUSTOMER PART NO.	CUSTOMER DWG NO.	MATL. SPEC.	TREAT. & FIN.	ISSUE MARK
YAZAKI					
OFFICE	OFFICE	OFFICE	NAME	TERMINAL	
VENDOR NO.	VENDOR NO.	VENDOR NO.	NAME	TERMINAL	
10MAX 150MAX 100MAX 250MAX 2500V	DWG TYPE	DWG DATE	UNIT	SCALE	PART NO.
A ±0.15 ±0.2 ±0.3 ±0.5 ±0.75 ±1.0	±0.1	19.01.16	1/1	3	7003-6000 ETC.
C ±0.3 ±0.5 ±0.8 ±1.2 ±1.5 ±2.0	±0.1	19.01.16	1/1	3	7003-6000 R
SPECIFIED	±0.3 ±0.5 ±0.8 ±1.2 ±1.5 ±2.0	19.01.16	1/1	3	7003-6000 R
⑤ ±0.5 ±0.8 ±1.5 ±2.5 ±3.0 ±4.0	±0.5	19.01.16	1/1	3	7003-6000 R

REV	DATE	REVISION RECORD	NO.	CHKD
1	90.05.14	設計	1	
2	90.05.17	設計	2	
3	90.05.17	設計	3	
4	90.01.16	設計	4	

A1