



3

2

1


NO.	YAZAKI PART NO. AND CH. CODE	C	D	E	F	APPLICABLE WIRE	MASS
1	7114-3250	9.60	6.60	△(9.50)	△(7.30)	△ AV 5~8, AVS 5	△(4.0 g)
2	7114-3251	7.20	4.80	△(8.70)	△(5.10)	△ AV 3, AVS 3, AVS 3f	△(3.6 g)



SEC. B-B

△ NOTES

- MATING FEMALE TERMINAL PART NO. : 7116-3250 ETC.
 - MATING CONNECTOR PART NO. : 7122-4110 ETC.
- : 7122-4310-30 ETC.



SEC. A-A

△ 2018/09/07	DELETED PART NO., ETC.	C18-Z097	G. M	CUSTOMER △	CUSTOMER PART NO.	CUSTOMER DWG NO.	MAT'L. △ COPPER ALLOY (t=0.6)	TREAT. △ TIN PLATING	ISSUE MARK
△ 2016/08/04	CHANGED APPLICABLE WIRE SIZE, ETC.	C16-Z607	A. Q	OFFICE △	OFFICE VENDOR	TRIAL PART NO. -----	NAME △ L TYPE MALE TERMINAL		
△ 2002/05/30	CHANGED TOLERANCE ETC.	C02-X619	K. U	VENDOR NO.					
△ 1990/01/29	RENEW	C90-L039	H. Y	DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE
LET	DATE	REVISION RECORD	NO.	CHKD					
GENERAL TOLERANCE									
10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT			
A ±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1			
B ±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1			
C ±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15			
SPECIFIED									
MASS									
△ SEE TABLE									
M. NAKAMURA									
APPROVED									
R									
NEW									
1983/03/10									
DRAWN									
INABA									
G. WANDERICO									
1983/03/11									
1983/09/07									
2018/09/07									
PART NO. 7114-3250 ETC.									
CH. CODE									
DWG NO. △ 7114-3250:R									
SET DWG NO.									
YAZAKI CORPORATION									

3

2

1