





TABLE 1	PART NUMBER	APPLICABLE WIRE SIZE (SINGLE CRIMP)		GRIP DIMENSIONS	
		AWG	mm ²	A	B
	7114-4102-06	22 - 20	0.35-0.5	2.50	4.85
	7114-4103-06	18 - 16	0.75-1.25	3.30	5.00



SECTION A-A



SECTION B-E

- NOTES:
1. PARTS MUST BE PURCHASED FROM YAZAKI.
 2. PART MUST BE FREE OF BURRS OR SHARP EDGES THAT MAY BE DETRIMENTAL TO SATISFACTORY ASSEMBLY, SAFE HANDLING OR FUNCTION OF PART.
 3. MATING TERMINAL: 7116-4102-06 ETC.
 4. MATERIAL: COPPER ALLOY.
 5. PLATING TREATMENT: 7114-4102-06 (Ag) SILVER PLATED AS SHOWN
7114-4103-06 (Sn) TIN PLATED AS SHOWN
7114-4103-06 (Ag) SILVER PLATED AS SHOWN
7114-4103-06 (Sn) TIN PLATED AS SHOWN
 6. PART DESIGNED TO SATISFY USCAR 2, REV. 6, FEBRUARY 2013, (CLASS 3)
 7. PART TO COMPLY WITH YPES-31-038 REQUIREMENTS.
 8. THIS DRAWING MUST BE USED FOR INTERNAL YAZAKI PSW SUBMISSION.

△	02-12-2014	NEW	C14-A062	GM
LET	DATE	REVISION RECORD	NO.	CHKD

GENERAL TOLERANCE											
	10 MAX	50 MAX	100 MAX	250 MAX	250 OVR	R5 MAX	R10 MAX	R20 MAX	R20 OVR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75	±0.2	±0.3	±0.5	±2.5	±3°	0.1
B	±0.2	±0.3	±0.55	±0.95	±1.4					±3°	0.1
(C)	±0.3	±0.5	±0.8	±1.4	±2.0					±3°	0.15
SPECIFIED										MASS	

CUSTOMER							MATL. SPEC.		TREAT. & FIN.	
CUSTOMER PART NO.				CUSTOMER DWG NO.			SEE NOTES		SEE NOTES	
OFFICE YNA				TRIAL PART NO.			NAME 1.5mm YESC			
VENDOR							-----			
VENDOR NO.							SEALED MALE TERMINAL			
DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE	PART NO. 7114-4102-06 ETC.				
R	7114-4102-02:M	02-12-2014	mm	5/1	3	DWG NO. 7114-4102-06:R				
APPROVED	CHECKED	CHECKED	DESIGN	DRAWN	DWG NO. 7114-4102-06:R					
			K. OHTAKA	GILBERTO MARINELARENA	YAZAKI CORPORATION					
			05-29-1995	02-12-2014						