

1

2

3

YAZAKI PART NO.	W ₁	H ₁	W ₂	H ₂	APPLICABLE WIRE SIZE
7116-2990-02	2.3	(2.6)	3.7	(2.9)	△CAVUS, CAVS 0.3~0.5
7116-2991-02	3.1	(3.1)	5.5	(4.9)	CAVUS, CAVS, AVS 0.85~1.25
7116-2992-02	4.3	(4.4)	6.5	(6.4)	AVS 2~3, AVSS 2

注 記

1. 対応品番 : 7114-2882-02

: 7114-2883-02



: 7114-2872-02

NOTE



1. MATING PART NO. : 7114-2882-02

: 7114-2883-02

: 7114-2872-02



7116-2992-02



SEC. B-B

SEC. C-C

SEC. A-A

		CUSTOMER		CUSTOMER PART NO.		CUSTOMER DWG NO.		MATL. SPEC.	△ BRASS (t=0.30)	TREAT. & FIN.	△ TIN PLATING	ISSUE MARK	
△	2011/08/28	CHANGED	NOTE ETC.	C11-Z601	G. M								
LET	1998/03/17	NEW		C98-L142	H. Y								
DATE		REVISION	RECORD	NO.	CHKD	OFFICE	TRIAL PART NO.	NAME MF-SN TERMINAL					
GENERAL TOLERANCE												VENDOR NO.	
10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT	DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE	PART NO.
±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1	R	NEW	1998/01/28	mm	5:1	3	7116-2990-02 ETC.
B ±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1	APPROVED	CHECKED	CHECKED	DESIGN	DRAWN	DWG NO.	SET DWG NO.
(C) ±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15	M. KASHIYAMA					7116-2990-02:R	
SPECIFIED					MASS		2011/08/28		2011/08/28	1997/12/25	2011/08/28	YAZAKI CORPORATION	

3