


1					2		3										
PART NO. AND CH. CODE	W ₁	H ₁	W ₂	H ₂	APPLICABLE WIRE SIZE	△5	△3	YAZAKI PART NO. AND CH. CODE	NO.	MATERIAL							
								7116-3250	6.60	(7.20)	9.60	(9.80)	△4, AV 5~8, AVS 5		7116-3250	-	COPPER ALLOY (t=0.60) TIN PLATING
								7116-3251	4.80	(5.20)	7.20	(8.80)	△4, AV 3, AVS 3, AVS 3f		7157-7270	①	STAINLESS STEEL (t=0.30)
								7116-3252	4.00	(4.30)	7.20	(8.80)	FLW 0.85~2				




記注

1. かん合オスターミナルNO. : 7114-3250 ETC.

NOTE

1. MATING MALE TERMINAL NO. : 7114-3250 ETC.



	2018/09/25	DELETED PART NO., ETC.	C18-P326	Y.M
5	2016/08/04	CHANGED APPLICABLE WIRE SIZE ETC.	C16-Z607	A.Q
4	2006/02/27	ADDED PART NO., ETC.	C06-Z227	K.U
3	1996/08/07	CHANGED DIMENSION	C96-6845	H.K
2	1993/11/08	CHANGED DWG. NO. ETC.	C93-7089	Y.I
1	1988/03/16	NEW	8MC-4033	M.Y
LET	DATE	REVISION RECORD	NO.	CHKD
GENERAL TOLERANCE				
	10MAX	50MAX	100MAX	250MAX
A	±0.15	±0.2	±0.3	±0.5
B	±0.2	±0.3	±0.55	±0.95
C	±0.3	±0.5	±0.8	±1.4
SPECIFIED	MASS			
	△ (3.5) g			

[illegible]