






1

2

3

YAZAKI PART NO.	COLOR
7123-2511	NATURAL
7123-2511-10	DARK GRAY
7123-2511-30	BLACK
7123-2511-40	LIGHT GRAY
7123-2511-50	RED
7123-2511-60	GREEN
7123-2511-70	YELLOW
7123-2511-80	BROWN
7123-2511-90	BLUE



注記

1. 適用端子番: 7116-2783, 7116-2784, 7116-2796-02

NOTE

1. APPLICABLE TERMINAL NO. : 7116-2783, 7116-2784, 7116-2796-02

ISSUE MARK

△	95. 11. 14	ADDED APPLICABLE TERMINAL NO.	C95-M668	Y. Y	CUSTOMER	CUSTOMER PART NO.		CUSTOMER DWG NO.		MATL. SPEC.	POLYAMIDE	TREAT. & FIN.		
	93. 01. 25	NEW	C93-L059	K. S	OFFICE	TRIAL PART NO.		NAME		250 1P HOUSING FEMALE				
LET	DATE	REVISION RECORD	NO.	CHKD	VENDOR	VENDOR NO.								
GENERAL TOLERANCE														
	10MAX	50MAX	100MAX	250MAX	250QVR	ANGLE	ECCENT	DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE	
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1	R	NEW	93. 01. 25	mm	2/1	3	
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1	APPROVED	CHECKED	CHECKED	DESIGN	DRAWN	PART NO.	
©	±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15	手書 稲葉 J1		手書 井内		IKEDA Y. OHKUBO		7123-2511 ETC.
SPECIFIED							MASS	手書 稲葉 J1		手書 井内		手書 井内		DWG NO.
							0.9 g	95. 11. 28		95. 11. 24		95. 11. 23		7123-2511:R
										85. 01. 22		95. 11. 14		YAZAKI CORPORATION

1

2

3