






| PART NO.     | COLOR        |
|--------------|--------------|
| 7123-2840    | NATURAL      |
| 7123-2840-70 | YELLOW       |
| 7123-2840-60 | GREEN        |
| 7123-2840-30 | BLACK        |
| 7123-2840-80 | BROWN        |
| 7123-2840-90 | BLUE         |
| 7123-2840-50 | RED          |
| 7123-2840-10 | △ DARK GRAY  |
| 7123-2840-40 | △ LIGHT GRAY |

注記

- 1)嵌合相手品番:7122-2840ETC.  
2)適用端子品番:7116-2640ETC.

NOTES

- 1)MATING PART NO:7122-2840ETC.  
2)APPLICABLE TERMINAL NO:7116-2640ETC.



|     |          |                           |          |      |
|-----|----------|---------------------------|----------|------|
| △   | 90.02.03 | ADDED PART NO.            | C90-L084 | H. Y |
| △   | 88.09.21 | ADDED PART NO.            | BMC-0450 | H. Y |
| △   | 88.07.07 | RENEW AND CHANGED DRAWING | BMC-3007 | S. Y |
| LET | DATE     | REVISION RECORD           | NO.      | CHKD |

| GENERAL TOLERANCE |       |       |        |        |        |       |        |  |  |
|-------------------|-------|-------|--------|--------|--------|-------|--------|--|--|
|                   | 10MAX | 50MAX | 100MAX | 250MAX | 2500VR | ANGLE | ECCENT |  |  |
| A                 | ±0.15 | ±0.2  | ±0.3   | ±0.5   | ±0.75  | ±30°  | 0.1    |  |  |
| B                 | ±0.2  | ±0.3  | ±0.55  | ±0.95  | ±1.4   | ±30°  | 0.1    |  |  |
| ◎                 | ±0.3  | ±0.5  | ±0.8   | ±1.4   | ±2     | ±30°  | 0.15   |  |  |
| SPECIFIED         |       |       |        |        | WEIGHT |       |        |  |  |

|                   |  |                  |  |                           |  |
|-------------------|--|------------------|--|---------------------------|--|
| CUSTOMER          |  | MATL. NYLON      |  | TREAT. & FIN.             |  |
| CUSTOMER PART NO. |  | CUSTOMER DWG NO. |  | SPEC.                     |  |
| OFFICE            |  | STDLIB NO.       |  | NAME                      |  |
| VENDOR            |  | VENDOR NO.       |  | 4POLE HOUSING FEMALE      |  |
|                   |  |                  |  | (WITH HOUSING LANCE LOCK) |  |
|                   |  |                  |  | PART NO. 7123-2840etc     |  |
|                   |  |                  |  | DWG NO. 7123-2840:R       |  |
|                   |  |                  |  | TRIAL PART NO.            |  |
|                   |  |                  |  | YAZAKI CORPORATION        |  |
|                   |  |                  |  | ISSUE MARK                |  |