




3

2

1

GENERAL TOLERANCE											
	10 MAX	50 MAX	100 MAX	250 MAX	250 OVR	R5 MAX	R10 MAX	R20 MAX	R20 OVR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75	±0.2	±0.3	±0.5	±2.5	±3°	0.1
B	±0.2	±0.3	±0.55	±0.95	±1.4	±0.2	±0.3	±0.5	±2.5	±3°	0.1
◎	±0.3	±0.5	±0.8	±1.4	±2					±3°	0.15



PART NO. AND CH. CODE	MATERIAL	COLOR
7186-8849-A	PBT	NATURAL
△ 7186-8849-10-A	PBT	DARK GRAY
△ 7186-8849-30-A	PBT	BLACK
△ 7186-8849-60-A	PBT	GREEN
△ 7186-8849-80-A	PBT	BROWN
△ 7186-8849-90-A	PBT	BLUE

注記

- △ 1. かん合相手品番 : 7187-8854 ETC.
- 2. 適用端子品番 : 7114-7386-02 ETC.

NOTES

- △ 1. MATING PART NO. : 7187-8854 ETC.
- 2. APPLICABLE TERMINAL PART NO. : 7114-7386-02 ETC.

B

A

LET	DATE	REVISION RECORD	NO.	CHKD
△	2015/03/13	ADDED COLOR NO.	C15-Z108	K.T
△	2014/04/21	ADDED PART NO.	C14-Z212	E.D
△	2012/04/20	ADDED COLOR NO.	C12-Z399	J.C
△	2012/02/09	ADDED COLOR NO. ETC.	C12-Z193	R.M
△	2012/01/11	CHANGED FORM. [A]	C12-Z059	J.C
△	2011/11/23	NEW	C11-Z633	G.M

GENERAL TOLERANCE						
10MAX	50MAX	100MAX	250MAX	250OVR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30'
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30'
C	±0.3	±0.5	±0.8	±1.4	±2	±30'

SPECIFIED

MASS

CUSTOMER	CUSTOMER PART NO.	CUSTOMER DWG NO.	OFFICE	TRIAL PART NO.	VENDOR	VENDOR NO.	DWG TYPE	DWG DATE	UNIT	SCL	ANGLE	PART NO. CH. CODE
							R	2011/11/23	mm	2:1	3	△ 7186-8849 ETC.
							APPROVED	CHECKED	DESIGN	DRAWN		DWG NO. 7186-8849:R
							T. MATSUNAGA	T. FUKAYA	K. MATSUMURA	K. TOBIAS		SET DWG NO.
							2015/03/13	2015/03/13	2011/09/04	2015/03/13		YAZAKI CORPORATION

ISSUE MARK

MATL. SPEC. △ SEE TABLE TREAT. & FIN.

NAME 060 4P HLC HOUSING MALE

3

2

1