






TABLE 1

SUB ASSEMBLY PART NO. AND CH. CODE	NO.	PART NO. AND CH. CODE	MATERIAL	COLOR	△ QTY.
7282-1054 ETC.	①	SEE TABLE 2	PBT	SEE TABLE 2	1
	②	7157-4343	PBT	NATURAL	1

TABLE 2

SUB ASSEMBLY PART NO. AND CH. CODE	PART NO. AND CH. CODE	COLOR
7282-1054. [A]	7182-1054	NATURAL
7282-1054-10. [A]	7182-1054-10	DARK GRAY
7282-1054-30. [A]	7182-1054-30	BLACK
7282-1054-40. [A]	7182-1054-40	LIGHT GRAY
7282-1054-50. [A]	7182-1054-50	ORANGE
7282-1054-90. [A]	7182-1054-90	BLUE

注 記

1. 適用端子品番: 090Ⅱ 7114-4020 ETC.
187 7114-4030 ETC.

△ 2. 嵌合相手品番: 7283-1054 ETC.

NOTES

1. APPLICABLE TERMINAL NO. : 090Ⅱ 7114-4020 ETC.
187 7114-4030 ETC.

△ 2. MATING PART NO. : 7283-1054 ETC.

ISSUE MARK

								CUSTOMER					MATL. SPEC.					TREAT. & FIN.				
								CUSTOMER PART NO.					CUSTOMER DWG NO.					SEE TABLE 1				
△	99.02.11	ADDED NOTE. [A]			C99-L398	T. M							NAME					090II 4P+187 1P HYBRID				
	92.05.29	NEW			C92-L425	T. T	OFFICE						TRIAL PART NO.									
LET	DATE	REVISION RECORD			NO.	CHKD	VENDOR										CONNECTOR SUB ASSEMBLY MALE					
GENERAL TOLERANCE							VENDOR NO.															
	10MAX	50MAX	100MAX	250MAX	250QVR	ANGLE	ECCENT	DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE	PART NO.								
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1	R	NEW	92.05.29	mm	2/1	3	7282-1054 ETC.								
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1	APPROVED	CHECKED	CHECKED	DESIGN	DRAWN	DWG NO.									
③	±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15	加藤	山梨	英司	Y. OHTA	KANAZAWA	7282-1054:R									
SPECIFIED							MASS										SET DWG NO.					
							g					99.03.11 99.03.10 99.03.09					89.02.28 99.02.11					
																	YAZAKI CORPORATION					