



3

2

1



注記
1) 適用端子品番 : 7114-4020 ETC.
2) 嵌合相手品番 : 7283-1020 ETC.

NOTES

1) APPLICABLE TERMINAL NO. : 7114-4020 ETC.
2) MATING PART NO. : 7283-1020 ETC.

SEC. B-B

SEC. A-A

Δ	98.07.09	ELIMINATED COLOR NO. CHANGED FORM.	C98-M221	T. M
LET	DATE	REVISION RECORD	NO.	CHKD
91.03.04	NEW	C91-L212	K. I	CHKD
GENERAL TOLERANCE				
10MAX	50MAX	100MAX	250MAX	2500VH
A	±0.15	±0.3	±0.5	±0.75
B	±0.2	±0.3	±0.55	±0.95
(C)	±0.3	±0.5	±0.8	±1.4
SPECIFIED				
MASS				
9				

CUSTOMER		CUSTOMER PART NO.		CUSTOMER DWG NO.	
OFFICE		TRIAL PART NO.		NAME	
VENDOR		VENDOR NO.		SUB ASSEMBLY MALE (CLAMP TYPE)	
DWG TYPE		DWG SOURCE		PART NO.	
R		NEW		CH. CODE	
APPROVED		CHECKED		DWG NO.	
H. HANAZAKI		M. YASUDA		SET DWG NO.	
98.07.16		98.07.16		YAZAKI CORPORATION	
98.07.16		98.07.16		7282-8823-90	
98.07.16		98.07.16		7282-8823-10	
98.07.16		98.07.16		7282-8823-30	
98.07.16		98.07.16		7282-8823-40	
98.07.16		98.07.16		7282-8823-50	
98.07.16		98.07.16		7282-8823-60	
98.07.16		98.07.16		7282-8823-90	

3

2

1