

3




2

1

TABLE 1		SUB ASSEMBLY PART NO. AND CH. CODE	NO.	PART NO. AND CH. CODE	MATERIAL	COLOR	QTY.
		7283-1061 ETC.	①	SEE TABLE 2	△ PBT	SEE TABLE 2	1
			②	7157-4098	△ PBT	NATURAL	1

TABLE 2		SUB ASSEMBLY PART NO. AND CH. CODE	PART NO. AND CH. CODE	COLOR
		7283-1061, □	7183-1061	NATURAL
		7283-1061-10, □	7183-1061-10	DARK GRAY
		7283-1061-30, □	7183-1061-30	BLACK
		7283-1061-40, □	7183-1061-40	LIGHT GRAY
		7283-1061-50, □	7183-1061-50	ORANGE
		7283-1061-60, □	7183-1061-60	GREEN
		7283-1061-90, □	7183-1061-90	BLUE

B



注記

1. 適用端子品番 : 7116-4020 ETC.

NOTE

1. APPLICABLE TERMINAL NO. : 7116-4020 ETC.

A

△	06/06/01	CORRECTION OF MATERIAL ETC.	C06-Z603	H. T
△	00/11/08	ELIMINATED COLOR NO.	C00-M346	Y. S
△	99/09/09	CORRECT ALL ERRORS	C99-M400	T. M
△	96/01/29	CHANGED FORM, □	C96-L183	Y. Y
△	90/11/10	NEW	C90-M210	M. H
LET	DATE	REVISION RECORD	NO.	CHKD
GENERAL TOLERANCE				
10MAX	50MAX	100MAX	250MAX	2500VR
±0.15	±0.2	±0.3	±0.5	±0.75
±30'	±30'	±30'	±30'	±30'
±0.2	±0.3	±0.55	±0.95	±1.4
±30'	±30'	±30'	±30'	±30'
±0.3	±0.5	±0.8	±1.4	±2
SPECIFIED				MASS
				9

CUSTOMER		CUSTOMER PART NO.	CUSTOMER DWG NO.	MAT'L. SPEC.	SEE TABLE 1	TREAT. & FIN.	ISSUE MARK
OFFICE		TRIAL PART NO.		NAME △ 2. 3Ⅱ 6P CONNECTOR			
VENDOR		VENDOR NO.		SUB ASSEMBLY FEMALE			
DWG TYPE		DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE	
R		NEW	90/11/10	m	2:1	3	
APPROVED		CHECKED	DESIGN	DRAWN	PART NO. 7283-1061 ETC.		
11月		三輪	Y. OHTA	L. LIM	CH. CODE		
06.06.02		06.06.01	88/12/13	06/06/01	DWG NO. 7283-1061:R		
					SET DWG NO.		
					YAZAKI CORPORATION		

1

2

3