





3

2

1

ASSEMBLY PART No. AND CH. CODE	NO.	PART No. AND CH. CODE	PART NAME	MATERIAL	COLOR	QTY.
7327-6166 [A] (50A-30A-40A)	①	7158-9209	COVER	PES	NATURAL	1
	②	7183-9750-90	HOUSING	PA6-T	BLUE	1
	③	7227-6127	FUSE ELEMENT SUB ASSEMBLY 50A	COPPER ALLOY	—	1
	④	7227-6125	FUSE ELEMENT SUB ASSEMBLY 30A	COPPER ALLOY	—	1
	⑤	7227-6126	FUSE ELEMENT SUB ASSEMBLY 40A	COPPER ALLOY	—	1



SEC. A-A

注記

1. 嵌合相手端子品番: 7114-2876

NOTE

1. MATING TERMINAL PART NO.: 7114-2876

A

A

GENERAL TOLERANCE									
10 MAX	50 MAX	100 MAX	250 MAX	250 OVR	R5 MAX	R10 MAX	R20 MAX	R20 OVR	ANGLE
A ± 0.15	± 0.2	± 0.3	± 0.5	± 0.75	± 0.2	± 0.3	± 0.5	± 2.5	$\pm 3^\circ$
B ± 0.2	± 0.3	± 0.55	± 0.95	± 1.4	± 0.2	± 0.3	± 0.5	± 2.5	$\pm 3^\circ$
C ± 0.3	± 0.5	± 0.8	± 1.4	± 2	± 0.2	± 0.3	± 0.5	± 2.5	$\pm 3^\circ$

LET	DATE	REVISION RECORD	NO.	CHKD	CUSTOMER	CUSTOMER PART NO.	CUSTOMER DWG NO.	MATL. SPEC.	SEE TABLE	TREAT. & FIN.
06/09/21	NEW [A]	C06-ZA38	K.T							

HIGH CURRENT FUSE LINKS (大電流ヒューズ)									
A1S 3P-TYPE ASSEMBLY 50A-30A-40A									
PART NO.		7327-6166 [A]		CH. CODE		7327-6166:R		SET DWG NO.	
DWG NO.		7327-6166:R		M. ADRIANO		05/09/14		06/09/21	
DESIGN		N. OHASHI		CHECKED		06.09.21		06/09/21	
APPROVED		I. OHASHI		DNG TYPE		R		DNG DATE	
DNG SOURCE		NEW		UNIT		mm		2:1	
SCAL		2:1		ANGLE		3		3	
MASS		g		SPECIFIED		0.15		0.15	
YAZAKI CORPORATION		YAZAKI CORPORATION		YAZAKI CORPORATION		YAZAKI CORPORATION		YAZAKI CORPORATION	

3

2

1