



Wiremold
Modulink™ 880MP Series Rectangular Plastic Floor Box with 2 Inch Conduit Opening
Part No. 880MP2



The Modulink™ nonmetallic floor box with 2 inch conduit feed provides power and communication services directly to the workstation or to any open space location. The Modulink™ Floor Box is a gangable box that allows a one-gang floor box to easily be turned into a two- or three-gang box simply by ganging together individual boxes. This floor box has many applications, some of which are commercial offices, retail stores, malls, financial and government institutions.

Features & Benefits

- 2" [51mm] conduit openings. Provides the largest conduit feed in the industry. Meets customer requirements for greater communication cable capacity.
- Conduit reducers and plugs provided. Allows direct reduction from 2" to 1 1/2" or 1 1/4" [51mm to 38mm or 32mm]. Reduces installation time by providing direct reduction and separate plugs by eliminating the need to cut out plugs to form reducers.
- Ratchet adjusting ring. Allows connection of cover flange without glue or mechanical fasteners. Reduces installation time and cost by providing 10° of post-pour adjustment of the cover flange.
- Modular design and gangability. One SKU to order boxes, with the ability to configure boxes as needed on the job site.
- Pass-through capability. Can feed multiple gangs from a single cable feed location. Reduces total installation time.
- Depth markings on exterior of the box. Makes floor box depth calculations quick and easy. Reduces installation time and labor costs.

Specifications

General Info

Product Line	Wiremold	Color	Black
UPC Number	786776180824	Country Of Origin	United States
Material	PVC	Construction	Assembled
Application Sector	Commercial	Standard	cULus Listed Nonmetallic Outlet Boxes: File E110748 Guide QCMZ.
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Floor Box

Dimensions

Product Width US	4.13 in	Product Weight US	3.5 lb
Product Volume US	212.95 cu in	Product Depth US	8.25 in

Product Height US	6.25 in	Cubic Capacity	100 in ³
-------------------	---------	----------------	---------------------

Knockout Size	1/2 in, 1-1/2 in
---------------	------------------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E110748	cULus Listed	Yes
---------------------	---------	--------------	-----

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

Technical Information

Floor Type	Carpet, Concrete, Tile	Service Capacity	Single
------------	------------------------	------------------	--------

Minimum Floor Depth	4 in	Box Capacity	1 Gang
---------------------	------	--------------	--------

Cable Entry	Conduit Hub, Knockout	Box Type	On-Grade
-------------	-----------------------	----------	----------

Number of Outlets	0	Depth Behind Device Plates	1.75 in
-------------------	---	----------------------------	---------
