



**Wiremold**  
**AC8840 Series Raised Floor Box**  
Part No. AC8840



This box has a 4" (102mm) depth design and can accommodate two duplex power receptacles on one side. Power plate with duplex knockouts included with box. The communication plate will accept two communication adapters for up to 12 ports of activation. Lids can be rotated 180° for easy orientation. Gray lids are die-cast zinc construction. NOTE: For custom options, consult factory. All boxes are sold with one power plate: 4" (102mm) deep boxes have plate with two power duplex receptacle KOs, 5" (127mm) deep boxes have plate with four power duplex receptacle KOs. All communication plates sold separately.

## Features & Benefits

This box has a 4" (102mm) depth design and can accommodate two duplex power receptacles on one side. Power plate with duplex knockouts included with box.

All boxes are sold with one power plate: 4" (102mm) deep boxes have plate with two power duplex receptacle KOs, 5" (127mm) deep boxes have plate with four power duplex receptacle KOs. All communication plates sold separately.

The communication plate will accept two communication adapters for up to 12 ports of activation. Lids can be rotated 180° for easy orientation. Gray lids are die-cast zinc construction.

NOTE: For custom options, consult factory.

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786564521389
Country Of Origin	United States	Material	Steel
Construction	Assembled	Cover Material	Die-Cast Zinc
Application Sector	Commercial	Standard	UL Listed Classified Raised Floor Box: File E2961 Guide QCIT, UL Listed Classified Raised Floor Box (prewired): File E51105 Guide QQVX, Meets Article 314 of NEC. Meets Article 12 2500 of CEC.
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Floor Box

### Dimensions

---

Product Width US	8.0 in	Product Weight US	10.9 lb
------------------	--------	-------------------	---------

---

Product Depth US	4.0 in	Product Length US	8.0 in
------------------	--------	-------------------	--------

---

Knockout Size	1/2 in, 3/4 in
---------------	----------------

---

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

---

### Trade Programs

---

USMCA	Yes
-------	-----

---

### Additional Information

---

RoHS Compliant	Yes
----------------	-----

---

### Technical Information

---

Floor Type	Raised	Service Capacity	Single
------------	--------	------------------	--------

---

Minimum Floor Depth	4 in	Box Capacity	2 Gangs
---------------------	------	--------------	---------

---

Cable Entry	Through Floor	Box Type	Recessed
-------------	---------------	----------	----------

---

Depth Behind Device Plates	1.5 in
----------------------------	--------

---