



Wiremold
AF3 Series Raised Floor Box
Part No. AF3-NC



The AF3 Raised Floor and Stage Floor Box provides four separate compartments that accommodate up to eight gangs of communication, power and/or audio/ video devices. The top panel has a unique built-in service divider that accommodates a combination power, communication and audio/video devices. These dividers are arranged in a single-double, single-gang configuration. The lower panel provides single-gang activation points in a single service configuration. Die-cast aluminum housing provides added strength and reliability. Polycarbonate hinged lid and trim flange are available for carpet or tile applications, as well as a color choice of black, brown, or gray.

Features & Benefits

The AF3 Raised Floor and Stage Floor Box provides four separate compartments that accommodate up to eight gangs of communication, power and/or audio/ video devices.

These dividers are arranged in a single-double, single-gang configuration. The lower panel provides single-gang activation points in a single service configuration.

The top panel has a unique built-in service divider that accommodates a combination power, communication and audio/video devices.

Die-cast aluminum housing provides added strength and reliability. Polycarbonate hinged lid and trim flange are available for carpet or tile applications, as well as a color choice of black, brown, or gray.

Specifications

General Info

| | | | |
|--------------------|--|----------------|---|
| Product Line | Wiremold | UPC Number | 786564519348 |
| Country Of Origin | United States | Material | Die-Cast Aluminum |
| Construction | Assembled | Cover Material | Polycarbonate |
| Application Sector | Commercial | Standard | UL Listed Classified Raised Floor Box: File E2961 Guide QCIT, UL Listed Classified Raised Floor Box (prewired): File E51105 Guide QQVX, Meets Article 314 of NEC. Meets Article 12 2500 of CEC. |
| Warranty Type | 1-Year from Installation or 2-Years from Day of Sale | Type | Floor Box |

Dimensions

| | | | |
|-------------------|--------|----------------|---------------------|
| Product Weight US | 7.0 lb | Cubic Capacity | 301 in ³ |
|-------------------|--------|----------------|---------------------|

| | |
|---------------|----------------|
| Knockout Size | 1/2 in, 3/4 in |
|---------------|----------------|

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|-------|--------------|-----|
| cULus ListingNumber | E2961 | cULus Listed | Yes |
|---------------------|-------|--------------|-----|

Trade Programs

| | |
|-------|-----|
| USMCA | Yes |
|-------|-----|

Additional Information

| | |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

Technical Information

| | | | |
|------------|----------------------|------------------|--------|
| Floor Type | Carpet, Raised, Tile | Service Capacity | Triple |
|------------|----------------------|------------------|--------|

| | | | |
|---------------------|------|--------------|---------|
| Minimum Floor Depth | 5 in | Box Capacity | 8 Gangs |
|---------------------|------|--------------|---------|

| | | | |
|-------------|---------------|----------|----------|
| Cable Entry | Through Floor | Box Type | Recessed |
|-------------|---------------|----------|----------|

| | |
|----------------------------|---------|
| Depth Behind Device Plates | 2.75 in |
|----------------------------|---------|
