



Wiremold

Exterior Box Cover Assembly, Single NEMA L6-30R Locking Receptacle, Brown (COVER ONLY)

Part No. XB814CL630BN



The brown Outdoor Ground Box cover assembly is prewired with (1) 30A L6-30R 240V corrosion-resistant duplex receptacles.

CAUTION: All ground box electrical circuits must be protected by a Ground Fault Circuit Interrupter upstream from the ground box.

NOTE: Cover must be closed while in use. Use only molded plug and cord assemblies that are rated for outdoor use.

NOTE: Maximum length of plug allowed at end of cord is 3" (76mm).

Features & Benefits

cUL Coming Soon UL listed to UL50E Type 6P (NEMA 6P) and IP68 requirements while in use ADA compliant Outdoor-rated construction Keeps receptacles and connections dry even when submerged

Specifications

General Info

Product Line	Wiremold	Color	Brown
UPC Number	786776187250	Country Of Origin	China
Material	Plastic	Number of Receptacles	1
Construction	Assembled	Features	ADA Compliant
Application Sector	Commercial, Education, Entertainment, Healthcare, Hospitality, Parks, Retail, Transit	Standard	UL Listed Outdoor In-Ground Boxes: File E486738 Guide QCNL.
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Ground Box Cover
Installed Devices	Locking Receptacle		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E486738	cULus Listed	Yes
---------------------	---------	--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Is Pre-Wired	Yes	Service Capacity	Single
--------------	-----	------------------	--------

Number of Gangs	1	Amperage	30 A
Enclosure Type	Type 6P	Load Capacity	5000 lb
NEMA Configuration Code	L6-30R		
