

SQR-UD5(ECC)

ECC UDIMM DDR5 5600(0 ~95°C)

NEW



Features

- JEDEC Standard 288-pin ECC UDIMM
- Data Transfer Rate: 5600 MT/s
- Original Samsung/Micron IC chip
- 30u" Golden Finger
- Lifetime Warranty
- Intelligent Monitoring Software Support

Specifications

DDR Type	DDR5
Pin / DIMM	288pin ECC UDIMM
Data Transfer Rate	5600 MT/s
Capacity	16/32/48GB
Power Supply	1.1V
Operating Temperature	0 ~ 95 °C

Ordering Information

PN	Description
SQR-UD5N16G5K6SEPB	288pin ECC UDIMM DDR5 5600 16GB 1.1v 2Gx8, (0 ~ 95 °C) Samsung
SQR-UD5N32G5K6SEPB	288pin ECC UDIMM DDR5 5600 32GB 1.1v 2Gx8, (0 ~ 95 °C), Samsung
SQR-UD5N48G5K6ME	288pin ECC UDIMM DDR5 5600 48GB 1.1v 3Gx8,(0 ~ 95 °C), Micron