






Connector Location A

Connector Location B



- Protection level: IP67/65
- Temperature range: -40°C ...+70°C

6.0 to 100	±1%
0.6 to 5.9	+0.04
0.2 to 0.5	+0.02
a [m]	Tolerance

length in "1m" step	100	XXX=000
	99	XXX=990
	.	.
	.	.
	12	XXX=120
length in "0.1m" step	11	XXX=110
	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	.	.
	0.5	XXX=005
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
Step	a [m]	XXX

HARTING PROFINET 4TP type B cable 8-wire Cat. 6A, PVC	09485252165XXX
Type of cable	Part no.

		All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing 2016-11-18		
	All rights reserved		Created by MUNTEANV	Inspected by POPESCUD	Standardisation AVRAM	Date 2016-12-07		State Final Release		
	Department HCS - RO		Title RJ Industrial Cable Assembly						Doc-Key / ECM-Nr. 100545993/UGD/003/E 500000112384	
HARTING Customised Solutions			Type TB	Number 09485252165XXX				Rev. E	Page 1/1	
D-32427 Minden										