



Connector Location A

Connector Location B




X
female



Loading Plan

- 1 brown
- 2 white
- 3 blue
- 4 black

- Protection level: IP67
- Temperature range: -25°C ... +80°C



4.0 to 100	±1%
0.1 to 3.9	+0.04
a [m]	Tolerance

length in "1m" step	100	XXX=000
	99	XXX=990
	.	.
	12	XXX=120
	11	XXX=110
length in "0.1m" step	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
	0.1	XXX=001
Step	a [m]	XXX

PVC grey, 4x0.25mm ²	21348100481XXX
Type of cable	Part no.

All rights reserved		Tech. Character.		Free size tol.		According to production drawing	
Department HCS - RO		Created by BANIUD Banciu	Inspected by 402676 Gross	Standardisation MUNTEANV Muntean	Date 2023-01-27	State Final Release	
HARTING Customised Solutions		Title M8 Cable Assembly 4-poles st/- f/-				Doc-Key / ECM-Nr. 100577970/UGD/009/C 500000236025	
D-32339 Espelkamp		Type TB	Number 21348100481XXX			Rev. C	Page 1/1