




4.0 to

0.1 to

a [

length in "1m" step	100	XXX=000
	99	XXX=990
	.	.
	.	.
	12	XXX=120
	11	XXX=110
length in "0.1m" step	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	.	.
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
	0.1	XXX=001
Step	a [m]	<u>XXX</u>

Part no.	2134B3008XXXXX
Type of cable	XX
PUR, green, 8xAWG24	XX=62

 All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing 2016-08-25	
 All rights reserved Department HCS - RO		Created by MUNTEANV	Inspected by POPESCUD	Standardisation AVRAM	Date 2016-10-18	State Final Release	
HARTING Customised Solutions D-32427 Minden		Title M12 A-coded Cable Assembly					Doc-Key / ECM-Nr. 100686746/UGD/000/A 500000110272
		Type TB	Number 2134B300862XXX				Rev. A