

har-modular shell housing 20



Image is for illustration purposes only. Please refer to product description.

Part number	02 09 500 2020
Specification	har-modular shell housing 20
HARTING eCatalogue	https://harting.com/02095002020

Identification

Category	Accessories
Series	har-modular®
Type of accessory	Shell housing

Version

Version	Top/side entry
Strain relief	With cable tie
Locking type	Locking lever
2 parts	Yes
Separable	Yes

Technical characteristics

Limiting temperature	-55 ... +125 °C
Degree of protection acc. to IEC 60529	IP20
Isolation group	III

Material properties

Material (hood/housing)	Thermoplastic resin (PC) Fibre-glass reinforced
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
Length	20.32 mm
RoHS	compliant

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Commercial data

Packaging size	10
Net weight	282.99 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140427327
eCl@ss	27440292 Connector component (accessories)
UNSPSC 24.0	39121400