

Uni-Dicht-Verschraubung Pg 11, 5-8mm



Image is for illustration purposes only. Please refer to product description.

Part number	09 00 000 5080
Specification	Uni-Dicht-Verschraubung Pg 11, 5-8mm
HARTING eCatalogue	https://harting.com/09000005080

Identification

Category	Accessories
Type of accessory	Cable gland

Technical characteristics

Tightening torque	≤10 Nm (depending on the cable and the seal insert used)
Wrench size	20
Limiting temperature	-40 ... +130 °C
Degree of protection acc. to IEC 60529	IP68
Size	Pg 11
Clamping range	5 ... 8 mm

Material properties

Material (cable glands)	Metal
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead 2-(2'-Hydroxy-3'-tert-butyl-5'-methylphenyl)-5-chlorobenzotriazole (UV-326)
California Proposition 65 substances	Yes



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Lead
	Nickel

Commercial data

Packaging size	10
Net weight	6.8 g
Country of origin	Germany
European customs tariff number	74122000
GTIN	5713140001619
eCl@ss	27140801 Screwed cable gland (electrical)
ETIM	EC000441
UNSPSC 24.0	39121431