

## Uni-Dicht-Verschraubung Pg21, 9-13mm



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 09 00 000 5091  |
| Specification      | Uni-Dicht-Verschraubung Pg21, 9-13mm  |
| HARTING eCatalogue | <a href="https://harting.com/09000005091">https://harting.com/09000005091</a> |

### Identification

|                   |             |
|-------------------|-------------|
| Category          | Accessories |
| Type of accessory | Cable gland |

### Technical characteristics

|  |  |
|--|--|
| Tightening torque                      | ≤15 Nm (depending on the cable and the seal insert used) |
| Wrench size                            | 30   |
| Limiting temperature                   | -40 ... +130 °C  |
| Degree of protection acc. to IEC 60529 | IP68   |
| Size                                   | Pg 21  |
| Clamping range                         | 9 ... 13 mm  |

### Material properties

|                                      |   |
|--------------------------------------|---|
| Material (cable glands)              | Metal   |
| RoHS                                 | compliant with exemption  |
| RoHS exemptions                      | 6(c): Copper alloy containing up to 4 % lead by weight                              |
| ELV status                           | compliant with exemption  |
| China RoHS                           | 50  |
| REACH Annex XVII substances          | Not contained   |
| REACH ANNEX XIV substances           | Not contained   |
| REACH SVHC substances                | Yes   |
| REACH SVHC substances                | Lead<br>2-(2'-Hydroxy-3'-tert-butyl-5'-methylphenyl)-5-chlorobenzotriazole (UV-326) |
| California Proposition 65 substances | Yes   |

## Material properties

|                                      |                |
|--------------------------------------|----------------|
| California Proposition 65 substances | Lead<br>Nickel |
|--------------------------------------|----------------|

## Commercial data

|                                |   |
|--------------------------------|---|
| Packaging size                 | 10  |
| Net weight                     | 67.764 g                                  |
| Country of origin              | Germany                                   |
| European customs tariff number | 74122000                                  |
| GTIN                           | 5713140001725                             |
| eCl@ss                         | 27140801 Screwed cable gland (electrical) |
| ETIM                           | EC000441                                  |
| UNSPSC 24.0                    | 39121431                                  |