

VERSCHRAUBUNG SKV 11



Image is for illustration purposes only. Please refer to product description.

Identification

Category	Accessories
Type of accessory	Cable gland
Description of the accessory	With strain relief

Technical characteristics

Wrench size	19
Degree of protection acc. to IEC 60529	IP68
Size	Pg 11
Width across corners	33 mm

Material properties

Material (cable glands)	Thermoplastic
Colour (cable gland)	RAL 7032 (pebble grey)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
ECHA SCIP number	60b1a572-bb3f-476f-9307-b7d1688bd90c
California Proposition 65 substances	Yes
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)

Material properties

Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)
------------------------------------	------------------------------

Commercial data

Packaging size	10
Net weight	7 g
Country of origin	Germany
European customs tariff number	39174000
GTIN	5713140002012
eCl@ss	27140801 Screwed cable gland (electrical)
ETIM	EC000441
UNSPSC 24.0	39121431