

## Han-Easy Lock ® 24B, SL



Image is for illustration purposes only. Please refer to product description.

Part number	09 00 000 5230
Specification	Han-Easy Lock ® 24B, SL
HARTING eCatalogue	<a href="https://harting.com/09000005230">https://harting.com/09000005230</a>

### Identification

Category	Accessories
Series of hoods/housings	Han® B
Type of accessory	Locking levers

### Version

Size	24 B
Locking type	Single locking lever
Han-Easy Lock®	Yes

### Material properties

Material (accessories)	Polycarbonate (PC) Stainless steel
Colour (accessories)	RAL 7037 (dust grey)
Material flammability class acc. to UL 94 (locking levers)	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
ECHA SCIP number	60b1a572-bb3f-476f-9307-b7d1688bd90c
California Proposition 65 substances	Yes

## Material properties

California Proposition 65 substances	Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Commercial data

Packaging size	10
Net weight	27.37 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140002333
eCl@ss	27440392 Connector (accessories)
ETIM	EC002939
UNSPSC 24.0	39121400