

har-SAB M12/8/4p PC



Image is for illustration purposes only. Please refer to product description.

Part number	09 07 000 2120 0
Specification	har-SAB M12/8/4p PC
HARTING eCatalogue	https://harting.com/090700021200

Identification

Series	Circular connectors M12
Element	Distribution boxes
Specification	Termination shell With LED green/yellow

Version

Total number of ports	8
Number of contacts	4

Technical characteristics

Rated current	9 A
Rated voltage	10 V DC 30 V DC
Limiting temperature	-30 ... +85 °C
Degree of protection acc. to IEC 60529	IP67
Number of channels per port	1
Circuit logic	PNP

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances Not contained

California Proposition 65 substances Yes

California Proposition 65 substances Nickel

Specifications and approvals

UL / CSA UL 2238 CYJV.E500416
CSA-C22.2 CYJV7.E500416

Commercial data

Packaging size 1

Net weight 339.95 g

Country of origin China

European customs tariff number 85371098

GTIN 5713140277151

eCl@ss 27440108 Passive Sensor-Actuator-Interface (with cable)

ETIM EC002585

UNSPSC 24.0 31251501