

## har-SAB M12/8/5p PAC 10m PVC w/o LED



Image is for illustration purposes only. Please refer to product description.

Part number	09 07 001 2225 000
Specification	har-SAB M12/8/5p PAC 10m PVC w/o LED
HARTING eCatalogue	<a href="https://harting.com/09070012225000">https://harting.com/09070012225000</a>

### Identification

Series	Circular connectors M12
Element	Distribution boxes
Specification	Pre-assembled master cable

### Version

Cable length	10 m
Core structure	3x AWG 18 + 16x AWG 22
Total number of ports	8
Number of contacts	5

### Technical characteristics

Rated current	9 A
Rated voltage	10 V DC 30 V DC
Limiting temperature	-30 ... +85 °C
Degree of protection acc. to IEC 60529	IP67
Number of channels per port	2
Circuit logic	PNP

### Material properties

Material (cable)	PVC
RoHS	compliant
ELV status	compliant

## Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

## Specifications and approvals

UL / CSA	UL 2238 CYJV.E500416 CSA-C22.2 CYJV7.E500416
----------	-------------------------------------------------

## Commercial data

Packaging size	1
Country of origin	China
European customs tariff number	85444290
GTIN	5713140277335
eCl@ss	27440108 Passive Sensor-Actuator-Interface (with cable)
ETIM	EC002585
UNSPSC 24.0	31251501