

## har-SAB M12/8/4p M23/12p



Image is for illustration purposes only. Please refer to product description.

Part number	09 07 002 2120 0
Specification	har-SAB M12/8/4p M23/12p
HARTING eCatalogue	<a href="https://harting.com/090700221200">https://harting.com/090700221200</a>

### Identification

Series	Circular connectors M12
Element	Distribution boxes
Specification	Master cable M23, 12 poles With LED green/yellow

### Version

Total number of ports	8
Number of contacts	4

### Technical characteristics

Rated current	9 A
Rated voltage	10 V DC 30 V DC
Limiting temperature	-30 ... +85 °C
Degree of protection acc. to IEC 60529	IP67
Number of channels per port	2
Circuit logic	PNP

### Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

## Specifications and approvals

UL / CSA	UL 2238 CYJV.E500416 CSA-C22.2 CYJV7.E500416
----------	---

## Commercial data

Packaging size	1
Net weight	301.19 g
Country of origin	China
European customs tariff number	85371098
GTIN	5713140277175
eCl@ss	27440108 Passive Sensor-Actuator-Interface (with cable)
ETIM	EC002585
UNSPSC 24.0	31251501