

har-SAB M12/4/5p M23/19p



Image is for illustration purposes only. Please refer to product description.

Part number	09 07 003 0220 0
Specification	har-SAB M12/4/5p M23/19p
HARTING eCatalogue	https://harting.com/090700302200

Identification

Series	Circular connectors M12
Element	Distribution boxes
Specification	Master cable M23, 19 poles With LED green/yellow

Version

Total number of ports	4
Number of contacts	5

Technical characteristics

Rated current	9 A
Rated voltage	10 V DC 30 V DC
Limiting temperature	-30 ... +85 °C
Degree of protection acc. to IEC 60529	IP67
Number of channels per port	2
Circuit logic	PNP

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

Specifications and approvals

UL / CSA	UL 2238 CYJV.E500416 CSA-C22.2 CYJV7.E500416
----------	---

Commercial data

Packaging size	1
Country of origin	China
European customs tariff number	85371098
GTIN	5713140276949
eCl@ss	27440108 Passive Sensor-Actuator-Interface (with cable)
ETIM	EC002585
UNSPSC 24.0	31251501