

## har-SAB M8/6/3p M12/8p



Image is for illustration purposes only. Please refer to product description.

Part number	09 07 005 1010 0
Specification	har-SAB M8/6/3p M12/8p
HARTING eCatalogue	<a href="https://harting.com/090700510100">https://harting.com/090700510100</a>

### Identification

Series	Circular connectors M8
Element	Distribution boxes
Specification	Master cable M12, 8 poles With LED green/yellow

### Version

Total number of ports	6
Number of contacts	3

### Technical characteristics

Rated current	6 A
Rated voltage	10 V AC 30 V AC
Limiting temperature	-25 ... +85 °C
Degree of protection acc. to IEC 60529	IP67
Number of channels per port	1
Circuit logic	PNP

### Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

## Commercial data

Packaging size	1
Net weight	120 g
Country of origin	China
European customs tariff number	85444290
GTIN	5713140276703
eCl@ss	27440108 Passive Sensor-Actuator-Interface (with cable)
ETIM	EC002585
UNSPSC 24.0	31251501